6. General Specifications:

Currency and

Protocol: See Software Description Document

Electrical Specification:

| Voltage | Max. Operating Current | Max. Current |
|---------|---------------------------|--------------|
| 24 V DC | 2.5 A | 4.0 A |

Use only current limiting CSA or UL approved Power Supply.

Operating

Temperature: -0 to +50 Degrees Celsius

Weight: < 15 kg (Without Cassette)

Weight of Cassette: 2.3 kg

Features: Multi-Width Validating Head

Bracket for Optional Lock for the Cassette End Switch for the Cassette and Cassette Lock

End Switch to the Chassis Runway Lights Bezel

Items

Enclosed: Bill-to-Bill Currency Management System

User Guide

Software Description

Prepare to Operation Instruction OPT-BB-INST

Security Locks Installation Instruction OPT-BB-INST-3

Lock Installation Kit OPT-MKFL-FLH1

Mounting Kit for Grounding Connection OPT-MKBB-GND

Wiring Harness OPT-HS-BB-CCNET

Optional: Sensor Box Extractor OPT-HW-FT01

Mounting Kit Outlet Connector OPT-MKBB-EA



1743 Linneman Road, Mount Prospect, IL 60056 USA PHONE: 1-847-952-5932 or 1-800-239-7017

bill-to-bill@suzohapp.com

http://www.suzohapp.com/Bill-to-Bill


© 2017 SUZOHAPP




Bill-to-Bill Currency Management System

MBB-0112

The Part Number on the Label includes Hardware Part Number and Software Part Number.





1. Assembly Contents:

| Unit | Part No. | Description |
|------------------------|------------------------|---|
| Validating Head | MFLV-9013 | With Multi-Width Centering Mechanism |
| Sense -A- Click | FLS-1706U FLS-1706L | Sense-A-Click Sensor Packs |
| Bezel | MFLB-4017 | Bezel with Runway Lights |
| Housing | BBH-3514 | 1000, Lock Bracket, Cassette and Lock Switches |
| Chassis | BBC-0110 | Holder for 3 Recycling Cassettes, Dispensing Cassette and Path Switch |
| Dispensing Cassette | BBD-0110 | Regular Plastic Bezel |
| Recycling Cassette | BBR-0110 | Storage from 80 to 110 Bills |
| Path Switch | BBS-0110 | Separating of Bills |
| MFL Power Interface | FLP-5711 | 24 V DC |
| B2B Power Interface | BBP-5713 | 24 V DC, RS-232 |

2. DIP Switch Setting:

DIP switches may be accessed by removing the Validating Head and opening the transparent cover at the rear. See Software Description for correct denominations and settings.


| SW No.1 | ON State | OFF State | Default |
|---------|--------------------|---------------------|---------|
| SW 1.1 | Bill Type 1 Enable | Bill Type 1 Disable | ON |
| SW 1.2 | Bill Type 2 Enable | Bill Type 2 Disable | ON |
| SW 1.3 | Bill Type 3 Enable | Bill Type 3 Disable | ON |
| SW 1.4 | Bill Type 4 Enable | Bill Type 4 Disable | ON |
| SW 1.5 | Bill Type 5 Enable | Bill Type 5 Disable | ON |
| SW 1.6 | Bill Type 6 Enable | Bill Type 6 Disable | ON |
| SW 1.7 | Bill Type 7 Enable | Bill Type 7 Disable | ON |
| SW 1.8 | Bill Type 8 Enable | Bill Type 8 Disable | ON |

| SW No.2 | ON State | OFF State | Default |
|---------|----------|--------------------|---------|
| SW 2.1 | Four Way | One Way | ON |
| SW 2.2 | Reserved | Reserved | ON |
| SW 2.3 | Reserved | Reserved | ON |
| SW 2.4 | Service | Host Communication | OFF |

3. Interface Connector Pinout:

Mating Connector: Socket 43645-1000 (Molex)

Socket 43645-1000 (Molex) Contact 43030-0008 (Molex)



| Terminal | Circuit |
|----------|-----------|
| 1 | + 24 V DC |
| 2 | + 24 V DC |
| 3 | 0 V DC |
| 4 | 0 V DC |
| 5 | GND |
| 6 | GND |
| 7 | TxD |
| 8 | RxD |
| 9 | M – RES |
| 10 | COMM GND |

4. Diagnostics:

Chart below lists the validator malfunctions, as indicated by the flashing bezel light:

| No. of Consecutive Flashes | Malfunction |
|-------------------------------|-------------------------------|
| 1 Green/ Red | COM Port CRC error |
| 2 Green/ Red | Internal CRC error |
| 3 Green/ Red | Improper Memory Stick |
| 4 Green/ Red | Memory Stick is absent |
| 5 Green/ Red | Improper type of Memory Stick |
| 6 Green/ Red | Download error |

5. Grounding:

- 1. Ground terminal must be connected to the host machine ground.
- 2. Use Mounting Kit OPT-MKBB-GND.
- 3. Connect grounding cable to screw shown. A copper wire of 14 12 AWG may also be used.

View A

